

# **Delay Line Interferometers**

#### **MINT and WT-MINT**

1
2
3
3
4
6
7
9
11
13
13
15
15
15
16
16
16
17

#### 1 – Description

The Micro Interferometer (MINT) is a Delay Line Interferometer (DLI) that performs the interference between an incoming signal and itself delayed by one bit-time. Dedicated to D(Q)PSK demodulation it can be used in many other applications. MINT is tunable to enable a precise matching of the carrier frequency. Two phase tuning options are available: the ultra-fast option (U), which exhibits very low tuning time constant (20µs), and the low voltage option (L), which needs only 3V to reach the tuning range.

The WT-MINT is a Widely Tunable MINT that enables to set the delay of the interferometer to the desired value. This can be done either with a micrometer head (manual option) or with a motorized translation stage (piloted version). In both case U and L option are available to precisely match the carrier frequency. There are three ranges of WT-MINT:

- WT-MINT 100ps: it enables to set an optical delay range of 100ps (corresponding to a Free Spectral Range of 10GHz to infinite, or for instance 5GHz to 10GHz). Available with manual or piloted option.
- WT-MINT 300ps: it enables to set an optical delay range of 300ps (corresponding to a Free Spectral Range of 3.3GHz to infinite, or 2.5GHz to 10GHz). Available with manual or piloted option.
- WT-MINT 3000ps: it enables to set an optical delay range of 3000ps (corresponding to a Free Spectral Range of 0.33GHz to infinite). Available with piloted option only.


MINT and WT-MINT products are also available with PM fibers.




MINT packaging


WT-MINT packaging

# 2 – Block diagrams





Block diagram: MINT



Block diagram: WT-MINT

The incoming signal is split in two parts. One is delayed regarding the other and then both are recombined on two outputs where they interfere one with each other. Both outputs are phase shifted by 180° and thus can be plugged to balanced or differential photodiodes that will convert a phase modulation into an amplitude modulation.

The delay between both arms of the interferometer should be equal to the time-bit ( $T_{bit}$ ) of the incoming signal. Then the interferometer is characterized by its Free Spectral Range (FSR) which is linked to  $T_{bit}$  by the relation FSR=1/ $T_{bit}$ .

#### 3 - Absolute maximum ratings

Parameter		Symbol	Min	Тур.	Max	Unit	Remarks/Conditions
Maximal optical input power		OpIn			300	mW	
Storage temperature	MINT	CTD	-40		80	°C	
range	WT-MINT	STR	-10		40		
Humidity		RH	5		85	%	Non condensing
Fiber bend radius			20			mm	
Maximum input voltage	U option	V			100	V	
	L option	V <sub>max</sub>			4		

#### 4 – Operating conditions

Parameter	Symbol	Min	Тур.	Max	Unit	Remarks/Conditions	
Operating wavelength		OWR	1520		1570	nm	
Operating temperature	MINT	OTD	0		70	0.0	
range	WT-MINT	OTR	10		35		

# 5 – MINT specifications

			MIN	T, FSR >	2.5GHz			
Parameter			Symbol	Min	Тур.	Max	Unit	Remarks/Conditions
Free Spectral Range <sup>1</sup>		FSR	2.5			GHz	Any FSR > 2.5GHz can be provided	
FSR accuracy <sup>1</sup>			ΔFSR			1	%FSR	
Insertion Losses <sup>1</sup>			IL			2.0	dB	
IL uniformity <sup>1</sup>			ΔΙL			0.5	dB	
Polarization Depe	ndant Lo	sses <sup>1,2</sup>	PDL			0.3	dB	
Polarization Dependant FSR>10GHz Frequency Shift <sup>1,2</sup>		PDFS			2.0	%FSR		
		FSR<10GHz				4.0		
Extinction Ratio <sup>1</sup>		ER	18			dB		
Polarization Extin	ction Rati	o <sup>1,3</sup>	PER	20	25		dB	
Temperature Dependant L U			TDFS			10	%FSR	
		U				50		
Tuning range					1.5	FSR		
Tuning voltage		L	V			3	V	Voltage needed to reach the tuning range
		U			75	90		
Tuning time cons	tant	L	- τ			0.02	s ms	To reach 50% of the final state
		L				0.5	1113	
Power consumpti	on	U	P			0.001	W	
Polarization Mod	e Dispersi	on	PMD			0.1	ps	
Chromatic Disper	sion		CD			1	ps/nm	
Optical Return Lo			ORL	35			dB	
Skew					0.5	1.0	ps	
	FSR >= 2	0GHz		4	14 x 26 x 9	.5		
Packaging size <sup>4</sup>				100 x 55 x 16			mm <sup>3</sup>	
Phase tuning con	nector			0.1 inch PIN header				
		SM			SMF-28			
Fiber Pigtail Type		PM			PANDA PN	/1		With 900µm loose tube
Fiber Pigtail Lengt	:h			0.9	1.0	1.1	m	

<sup>&</sup>lt;sup>1</sup> measured over OTR and OWR for all states of polarization <sup>2</sup> for Single Mode MINT <sup>3</sup> for Polarization Maintaining MINT <sup>4</sup> excluding fiber boot

www.kylia.com MINT & WTMINT


		MIN	T, FSR <	2.5GHz			
Parameter		Symbol	Min	Тур.	Max	Unit	Remarks/Conditions
Free Spectral Range <sup>1</sup>		FSR	0.4		2.5	GHz	Any FSR between 400MHz and 2.5GHz can be provided
FSR accuracy <sup>1</sup>		ΔFSR			5	%FSR	
Insertion Losses on short	arm <sup>1</sup>	IL1			9.0	dB	Including 6dB of natural
Insertion Losses on long	arm <sup>1</sup>	IL2			9.0	dB	losses due to beamsplitter
Polarization Extinction Ra	atio <sup>1,3</sup>	PER	20	25		dB	
Tuning range					1.5	FSR	
Tuning voltage	L	v			3	V	Voltage needed to reach the tuning range
Tuning voltage	U	V		75	90	_ v	
Tuning time constant	L				1.0	s ms	To reach 50% of the final state
Tuning time constant	U	τ			0.02		
Power consumption	L	Р			0.5	W	
rower consumption	U	r			0.001	VV	
Polarization Mode Disper	rsion	PMD			0.1	ps	
Chromatic Dispersion		CD			1	ps/nm	
Optical Return Loss		ORL	35			dB	
Skew				0.5	1.0	ps	
Packaging size <sup>4</sup>			13	30 x 65 x 1	9.5	mm <sup>3</sup>	
Phase tuning connector			0.1 i	nch PIN he	eader		
Fiber Distail Trees	SM			SMF-28			With 000 and lease to be
Fiber Pigtail Type	PM			PANDA PN	/1		With 900μm loose tube
Fiber Pigtail Length			0.9	1.0	1.1	m	

<sup>&</sup>lt;sup>1</sup> measured over OTR and OWR for all states of polarization <sup>2</sup> for Single Mode MINT <sup>3</sup> for Polarization Maintaining MINT <sup>4</sup> excluding fiber boot

www.kylia.com MINT & WTMINT

#### 6 - MINT statistic data

Here are the statistic data of our MINT delivered between January 2009 and March 2013 (any FSR from 2.5Hz to 100GHz, any phase tuning option).



For PDFS and ER, we do not observe Gaussian repartition because these parameters depend on the FSR (larger is the FSR, better are PDFS and ER).

# 7 – WT-MINT specifications

The 100ps WT-MINT allows a tunable FSR from 10GHz to infinite.

		WT-N	ИINT, 100	ps Opti	cal Dela	y Range	e	
Parameter			Symbol	Min	Тур.	Max	Unit	Remarks/Conditions
Optical Delay Range			ODR	100			ps	
Manual	WT-MINT ODR s	ensitivity				8	fs	
ρ⊢	Minimum incre	mental motion				2	fs	
Motorized WT-MINT	Relative accurac	СУ				75	fs	
loto VT-N	Unidirectional r	epeatability				15	fs	
2 >	Bidirectional rep	peatability				20	fs	
Insertio	on Losses <sup>1</sup>		IL			2.5	dB	
IL unifo	rmity <sup>1</sup>		ΔIL			0.5	dB	
Polariza	ation Dependant	Losses <sup>1,2</sup>	PDL			0.5	dB	
Polariza	ation Dependant	Frequency Shift <sup>1,2</sup>	PDFS			3.0	%FSR	
Extinction Ratio <sup>1</sup>		ER	18			dB		
Polarization Extinction Ratio <sup>1,3</sup>		PER	20	25		dB		
Tuning range					1.5	FSR		
	L	1,,			3	V	Voltage needed to reach	
Tuning	voitage	U	V		75	90	V	the tuning range
T	*i	L	_			1.0	S	To reach 50% of the final
runing	time constant	U	τ			0.02	ms	state
Dower	non cumention	L	P			0.5	w	
Power	consumption	U	P			0.001	VV	
Polariza	ation Mode Dispe	rsion	PMD			0.1	ps	
Chroma	atic Dispersion		CD			1	ps/nm	
Optical	Return Loss		ORL	35			dB	
Skew					0.5	1.0	ps	
Packagi	ng size <sup>4</sup>			216 x 92 x 40		mm <sup>3</sup>		
	uning connector			BNC				
Fiber P	stail Tuns	SM			SMF-28			With 000 up laces to be
riber Pi	gtail Type	PM		P	ANDA P	М		With 900µm loose tube

 $<sup>^{\</sup>rm 1}$  measured over ODR, OTR and OWR for all states of polarization  $^{\rm 2}$  for Single Mode WT-MINT

<sup>&</sup>lt;sup>3</sup> for Polarization Maintaining WT-MINT

<sup>&</sup>lt;sup>4</sup> excluding micrometer head or piloted actuator

The 300ps WT-MINT allows a tunable FSR from 3.3GHz to infinite or 2.5GHz to 10GHz.

		WT-N	лINT, 300	ps Opti	cal Dela	y Range	2	
Parameter			Symbol	Min	Тур.	Max	Unit	Remarks/Conditions
Optical Delay Range		ODR	300			ps		
Manual	WT-MINT ODR ser	nsitivity				15	fs	
ρL	Minimum increm	ental motion				3	fs	
Motorized WT-MINT	Relative accuracy					150	fs	
loto VT-N	Unidirectional rep	eatability				30	fs	
≥ >	Bidirectional repe	atability				40	fs	
Insertio	n Losses <sup>1</sup>		IL			4.0	dB	
IL unifo	rmity <sup>1</sup>		ΔIL			1.0	dB	
Polariza	ation Dependant Lo	osses <sup>1,2</sup>	PDL			0.8	dB	
Polariza	ation Dependant Fr	equency Shift <sup>1,2</sup>	PDFS			5.0	%FSR	
	on Ratio <sup>1</sup>		ER	15			dB	
Polarization Extinction Ratio <sup>1,3</sup>		PER	20	25		dB		
Tuning range					1.5	FSR		
	1.	L	V			3	V	Voltage needed to reach the tuning range
Tuning	voltage	U			75	90		
T	ti	L				1.0	S	To reach 50% of the final
runing	time constant	U	τ			0.02	ms	state
Davisaria		L	D			0.5	\A/	
Power	consumption	U	Р			0.001	W	
Polariza	ation Mode Dispers	ion	PMD			0.1	ps	
Chroma	atic Dispersion		CD			1	ps/nm	
Optical	Return Loss		ORL	35			dB	
Skew					0.5	1.0	ps	
Packaging size <sup>4</sup>			216 x 92 x 40		mm <sup>3</sup>			
Phase t	uning connector				BNC			
File and Di	-1-11 To	SM			SMF-28			NA/Sels 0000
Fiber Pigtail Type PM		PM		Р	ANDA PI	М		With 900µm loose tube

<sup>&</sup>lt;sup>1</sup> measured over ODR, OTR and OWR for all states of polarization <sup>2</sup> for Single Mode WT-MINT <sup>3</sup> for Polarization Maintaining WT-MINT <sup>4</sup> excluding micrometer head or piloted actuator


The 3ns WT-MINT allows a tunable FSR from 0.33GHz to infinite. The 12ns WT-MINT allows a tunable FSR from 83MHz to infinite.

	WT-M	INT, 3ns to	12ns O	ptical D	elay Ra	nge	
Parameter		Symbol	Min	Тур.	Max	Unit	Remarks/Conditions
Optical Delay Range		ODR	3000			ps	
Minimum incremental	3ns delay				10	fs	
motion	12ns delay				40	15	
Deletive e equipou	3ns delay				250	fs	
Relative accuracy	12ns delay				1000	15	
Unidirectional	3ns delay				30	fs	
repeatability	12ns delay				120	TS	
Didirectional repeatability	3ns delay				150	fo	
Bidirectional repeatability	12ns delay				600	fs	
Insertion Losses on short a	rm <sup>1</sup>	IL1			9.0	dB	Including 6dB of natural
Insertion Losses on long arm <sup>1</sup>		IL2			9.0	dB	losses due to beamsplitter
Polarization Extinction Ratio <sup>1,2</sup>		PER	20	25		dB	
Tuning range					1.5	FSR	
	L	V			3	V	Voltage needed to reach the tuning range
Tuning voltage	U	v		75	90		
Tuning time constant	L				1.0	S	To reach 50% of the fina
Tuning time constant	U	τ			0.02	ms	state
Power consumption	L	P			0.5	w	
Power consumption	U	P			0.001	VV	
Polarization Mode Dispersi	ion	PMD			0.1	ps	
Chromatic Dispersion		CD			1	ps/nm	
Optical Return Loss		ORL	35			dB	
Skew				0.5	1.0	ps	
Packaging size			750 x 400 x 129				
Phase tuning connector			BNC				
Fiber Dieteil Ture	SM		SMF-28				With 000 and lane to be
Fiber Pigtail Type	PM		Р	ANDA P	М		With 900µm loose tube

 $<sup>^{\</sup>rm 1}$  measured over ODR, OTR and OWR for all states of polarization  $^{\rm 2}$  for Polarization Maintaining WT-MINT

## 8 - Phase tuning options

For DPSK demodulation, the phase tuning is essential in order to control the contrast between both outputs of the interferometer/demodulator.




The FSR variation is not significant (and can be considered as invariant) when the user adjust the phase of the demodulator/interferometer.

KYLIA proposes for all its DPSK demodulators (MINT and WT-MINT) two different phase tuning options:

**U option:** Ultra-fast response based on a piezo actuator.

This option is helpful for fast shifting systems (instability of the laser for instance). The DLI can adapt itself instantaneously to the environment, if a closed loop between BER and phase shifting is set up. This solution is mainly used in labs.

With this option, the user can accomplish a shift of one FSR by applying a 60V voltage. The tuning time is better than  $20\mu s$ .



Tuning speed for a U option DPSK demodulator

**L option:** Low-voltage tuning based on a resistive heater


Phase shift is obtained using a resistive heater fixed on an optical element. Changing the voltage changes the local temperature and thus the optical index, then the optical delay.

With this option, the user can accomplish a shift of one FSR by applying a 2V voltage. The tuning time is better than 1s.

#### 9 – ER attenuation option


It is possible to tune the extinction ratio of an interferometer by adjusting the power in both arms. When the power is the same the ER will be the greatest. By attenuating the power in one arm, ER will be reduced.

The ER attenuation option for MINT and WT-MINT consist of a micrometer head that can adjust the power of one arm of the interferometer. It enables to tune the ER down to 0dB (one arm is totally shut down) with an accuracy of 1dB.




Block diagram: DLI with ER attenuation option


On the following graph, we show the variation of the spectral response of our DLI by attenuating the optical beam for one arm of the interferometer.



MINT spectral response with ER attenuation




MINT with ER attenuation option



WT-MINT with ER attenuation option

#### 10 – IL attenuation option


IL attenuation enables to increase the IL on each output individually. This can be done thanks to a micrometer head. The attenuation can be total (no power exits from the output) and adjusted with an accuracy of 0.1dB.




Block diagram: DLI with IL attenuation option

#### 11 – Tunable coupling option

This option is available for PM MINT or PM WT-MINT only. It enables to adjust the splitting ratio of the interferometer (which is 50/50 for standard interferometers) from 100/0 to 0/100. This can be very useful if a precise 50/50 ratio is needed.




Block diagram: DLI with tunable coupling option



WT-MINT PM with tunable coupling and ER attenuation options

## 12 - TAP option


Thanks to the flexibility of our technology, we can propose to add optical TAP outputs in our products. The TAP ratio can be 4% or 50%.



Block diagram: MINT with TAP option for input and output signals

# 13 - Second input option

A second input can also be added in our product.



Block diagram: MINT with a second optical input

#### 14 - Wavelength range

MINT and WT-MINT can be proposed at different wavelength range, from the visible to the IR 800nm, 1064nm, 1300nm...). The device will be operational on a wavelength range of a tens of nanometers centered on the wavelength required by customer.

#### 15 – Fiber type and connectors


Every MINT or WT-MINT can be proposed either with SM or PM fibers.


The devices can be proposed with any kind of connectors (FP/UPC, FC/APC, SC/PC, SC/APC, LC/PC, E2000/PC, E2000/APC, etc...).

## 16 – Custom products

Thanks to our free-space technology we can easily customize most of our products and so it is for the MINT and WT-MINT. Customer can feel free to ask for any customization they need. We will examine the request and do our best to have a positive answer.


# 17 - Packages layout






MINT packaging: FSR > 20GHz

MINT packaging: FSR > 2.5GHz



MINT packaging: FSR < 2.5GHz



WT-MINT packaging (with ER attenuation option)

#### 18 - Revision

date	version	Object
March 21, 2013	MINT V1.0	Creation
May 15, 2014	MINT V1.1	Phase tuning option explanation
		MINT packaging for FSR < 2.5GHz
February 3 <sup>rd</sup> , 2015	MINT V1.2	Added 12ns delay WTMINT